

Flat magnet with internal thread, SmCo₅, Ø: 20mm



Order data

Order number	GG5922 20
GTIN	
Item class	00N

Description

Version:

- Temperature-resistant up to maximum 200 °C.
- Galvanised surface, magnetic core made of samarium-cobalt (SmCo₅).
- Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.

Feature:

Contents: 10 pieces

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Ø	20 mm
maximum temperature resistance	200 °C
Threaded socket	yes
Thread	M4
Weight	16.5 g
Height with thread	13 mm

Height	6 mm
Material of the surface	galvanised
Nominal clamping force	90 N
Material of the magnet core	SmCo ₅
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread 10 pieces Thread M4	085921 M4
Flat magnet with internal thread Ø 20 mm	085922 20