



Value pack flat pot magnet with keeper plate



Order data

Order number	GG5944 29
GTIN	4067263137733
Item class	GGN

Description

Version:

- Flat magnet in a protective steel jacket.
- Magnet fixed from below via countersunk hole.
- Magnetic material temperature-resistant up to maximum 450°C (size 19 up to 100°C).

Feature:

Contents: 10 pieces

Application:

Jigs and fixtures.

Technical description

Nominal clamping force	50 N
Attachment hole Ø	5.2 mm
Ø	28.5 mm
Height	8.7 mm
Material of the surface	Stone
Material of the magnet core	AlNiCo

Type of product

Pot magnet

Accessories

Flat pot magnet with keeper plate Ø 29 mm

085944 29