

**Instant adhesive, 20 g, Type: UNI****Order data**

Order number	GG3361 UNI
GTIN	4067263137764
Item class	00N

**Description****Version:**

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity. For general purpose use, suitable for most **plastics, metal and wood.**

**Feature:**

Contents: 5 pieces

**Note:**

Not available in all countries. Express delivery not available.

**Technical description**

Chemical basis	Ethyl cyanoacrylate
Suitable for material	wood
Suitable for material	Metal
Suitable for material	Plastic
Storage temperature	20 °C

Capacity	20 ml
Working life after date of manufacture	9 mo
Density	1.06 g/cm <sup>3</sup>
Functional strength to	10 - 30 min
Touch dry after	5 - 40 s
Tensile strength	10 - 20 N/mm <sup>2</sup>
Operating temperature range	-55 - 95 °C
Colour	transparent
Shape	liquid
Dynamic viscosity	95 - 200 mPas
Labelling of hazardous substances	GHS07: Exclamation mark
Tensile shear strength	10 - 20 N/mm <sup>2</sup>
Product name attribute	20 g
Type of product	Instant adhesive

---

## Accessories

Instant adhesive Type UNI	083361 UNI
---------------------------	------------