


TMSERROR, Grit equivalent: 40mm

Order data

Order number	GG5880 40
GTIN	4067263137795
Item class	00N

Description
Version:

Abrasive roller Ø 100x100 mm with flap strips of abrasive cloth. Mounting bore Ø 19 mm with multiple splines.

similar to 568480.

Sinusoidal abrasive fleece without cut edges.

Feature:

Contents: 10 pieces

Function:

Individual keys means each key can open and close only **one** lock or cylinder, i.e. the key is unique.

Application:

Sinusoidal fleece – for matting and polishing without abrupt changes in texture (**same as 568480**).

Content:

8 rollers / bulk pack.

Supplied with:

Padlock with 3 keys.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 drum.

For matching the width of narrow rollers Ø 100x50 mm use the spacer ring pack No. 56 8439.

Technical description

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Roller Ø	100 mm
Roller width	100 mm
Product name attribute	Ø 100 × 100 mm
Type of product	Abrasive flap wheel roller, fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Carbide (HM)	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

Accessories

Cylinder padlock individual keys Body Ø 40 mm

085880 40