

**Garant****GARANT GreenPlus ultrasonic cleaner Sonic Cleaner N, neutral, Contents: 5l****Order data**

Order number	GG8017 5
GTIN	4067263137870
Item class	00N

**Description****Version:**

GARANT GreenPlus **ultrasonic cleaner** – top performance with maximum flexibility. Do you work with complex workpiece geometries and delicate surfaces? Then the Sonic Cleaner series is made for you. The cleaning series from GARANT GreenPlus, specially designed for ultrasonic systems, includes alkaline, acid and neutral cleaners for a wide variety of materials and fields of application. Depending on the requirements and degree of dirt, the highly concentrated cleaners can be diluted and are powerful even at room temperature. This makes optimum use of the medium. Their long service life also saves time and money. All Sonic Cleaners are **hazard-label-free, biologically degradable, VOC-free and silicate-free**. For companies, this means the products are easy to handle and ensures both your employees and the environment are protected.

Sonic Cleaner N, **neutral** cleaning concentrate for particularly gentle cleaning of sensitive materials such as aluminium, non-ferrous metals, painted and galvanized surfaces.

**Feature:**

Contents: 5 pieces

**Application:**

For ultrasonic cleaning baths.

Light contamination such as greases and machining oils, grinding, polishing and lapping agents, fingerprints, grinding dust.

**Suitable for:**

Sensitive materials such as aluminium, non-ferrous metals, painted and galvanized surfaces, but also steel, stainless steel, plastic, glass, ceramic and rubber.

## Technical description

pH value	9.6
Storage temperature	20 - 60 °C
Sustainability	GARANT GreenPlus
Fill capacity liquid	5 l
Mixing ratio	2 – 5 %
Series	GreenPlus
Product name attribute	neutral
Type of product	Ultrasonic power cleaner

## Accessories

GARANT GreenPlus ultrasonic cleanerSonic Cleaner N Contents 5 l	088017 5
--	----------