

Garant**GARANT GreenPlus ultrasonic cleaner Sonic Cleaner AC, Acid, Contents: 5l****Order data**

Order number	GG8018 5
GTIN	4067263137887
Item class	00N

Description**Version:**

GARANT GreenPlus **ultrasonic cleaner** – top performance with maximum flexibility. Do you work with complex workpiece geometries and delicate surfaces? Then the Sonic Cleaner series is made for you. The cleaning series from GARANT GreenPlus, specially designed for ultrasonic systems, includes alkaline, acid and neutral cleaners for a wide variety of materials and fields of application. Depending on the requirements and degree of dirt, the highly concentrated cleaners can be diluted and are powerful even at room temperature. This makes optimum use of the medium. Their long service life also saves time and money. All Sonic Cleaners are **hazard-label-free, biologically degradable, VOC-free and silicate-free**. For companies, this means the products are easy to handle and ensures both your employees and the environment are protected.

Sonic Cleaner AC – **acid, odourless** cleaning concentrate, is used to remove rust from ferrous materials. In addition, lime, oxides and mineral deposits can be removed.

Feature:

Contents: 5 pieces

Application:

For ultrasonic cleaning baths.

Rust, limescale, oxides, mineral deposits as well as oils and greases.

Suitable for:

These materials are coated with a protective film of a molecular thickness, which temporarily protects them against corrosion. Subsequent coatings or hardening processes are unaffected.

Technical description

Sustainability	GARANT GreenPlus
Storage temperature	20 - 80 °C
Series	GreenPlus
Fill capacity liquid	5 l
pH value	2.2
Mixing ratio	5 – 100 %
Product name attribute	Acid
Type of product	Ultrasonic power cleaner

Accessories

GARANT GreenPlus ultrasonic cleanerSonic Cleaner AC Contents 5 l	088018 5
---	----------
