

**Value pack quick-release coupling with external thread****Order data**

Order number	GG0170 1/2
GTIN	4067263138075
Item class	GGN

Description**Version:**

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Feature:

Contents 10 pieces

Technical description

Flow rate	1000 l/min
Connection external thread	1/2 in
maximum operating pressure	35 bar
Type of product	Coupling

Accessories

Quick connect
thread 1/2 in

With external thread
Connection external

080170 1/2