

**Basic set, T-slot nominal size / thread: 14/M12mm****Order data**

Order number	375450 14/M12
GTIN	4067263133315
Item class	32X

**Description****Version:**

Annealed screw parts, strength class 8.8.

**Content:**

Clamping heights at 2 clamping points in mm: 150

Clamping heights at 4 clamping points in mm: 115

Step clamp: 2 pcs. size 14×100 mm; 2 pcs. size 14×150 mm

Screws for T-slots strength class 8.8: 4 pcs. M12×14×50 mm; 4 pcs. M12×14×125 mm

Clamping blocks, serrated L×W×H in mm: 4 pcs. size 2 (38×31×66); 4 pcs. size 3 (67×31×117)

Clamping spindle strength class 8.8 in mm: 4 pcs. M12×125

Hexagonal nut (1.5 d tall): 4 × M12

Washer for clamping tools: 4 × M12

Extension nut: 4 × M12

Weight in kg: 8,5

External dimensions of box in mm: 275×125×65

**Technical description**

Type of product	Clamping screw
-----------------	----------------

