



Basic set, T-slot nominal size / thread: 16/M14mm



Order data

Order number	375450 16/M14
GTIN	4067263133322
Item class	32X

Description

Version:

Annealed screw parts, strength class 8.8.

Content:

Clamping heights at 2 clamping points in mm: 178

Clamping heights at 4 clamping points in mm: 135

Step clamp: 2 pcs. size 14×100 mm; 2 pcs. size 14×150 mm

Clamping blocks, serrated L×W×H in mm: 4 pcs. size 2 (38×31×66); 4 pcs. size 3 (67×31×117)

Screws for T-slots strength class 8.8: 4 pcs. M14×16×100 mm; 4 pcs. M14×16×160 mm

Clamping spindle strength class 8.8 in mm: 4 pcs. M14×100

Hexagonal nut (1.5 d tall): 4 × M14

Washer for clamping tools: 4 × M14

Extension nut: 4 × M14

Weight in kg: 9.3

External dimensions of box in mm: 213×153×109

Technical description

Type of product	Clamping screw
-----------------	----------------

