



## Screw jack set Quenched and tempered steel., Type: 14mm



---

### Order data

Order number	373560 14
GTIN	4020772428860
Item class	35A

---

### Description

**Version:**

The modular design allows the use of various screw jack intermediate and base elements, which are bolted together by the inserted thread. The individual elements are fixed in a reliable manner using a c-hook spanner. With this set, a maximum height of 285 mm can be achieved.

**Advantage:**

- Maximum height of 422 mm can be achieved with additional intermediate elements.
- Improved handling through individual elements.
- Reduction of setting-up time through part flexibility.
- Optimisation of warehousing.

**Content:**

Screw jack with flat support: Size 52; H<sub>min</sub> 42 mm; H<sub>max</sub> 52 mm; TR 30x4; D1 50; D2 50; M38x 2

Size 70; H<sub>min</sub> 50 mm; H<sub>max</sub> 70 mm; TR 30x4; D1 50; D2 50; M38x 2

Size 100; H<sub>min</sub> 70 mm; H<sub>max</sub> 100 mm; TR 30x4; D1 50; D2 50; M38x 2

Base element: Size M12x 14; A 14 mm; G M12 mm; H 10 mm

Intermediate element: Size 25; D1 50 mm; H 25 mm; H1 35 mm

Size 50; D1 50 mm; H 50 mm; H1 60 mm

Size 100; D1 50 mm; H 100 mm; H1 110 mm

Ball pad 6440G-M10: H 10 mm; D1 39 mm; D2 11.9 mm; G1 M10; H1 32 mm; H2 22 mm

C-hook/pin spanner: DIN1810B 45-50

**Note:**

Maximum achievable height of 422 mm with a permissible support force of 100 kN; there is also a risk of buckling. Do not adjust under load.

---

## Technical description

Type of product

Screw jack