

**Basic set, T-slot nominal size / thread: 18/M16mm****Order data**

Order number	375450 18/M16
GTIN	4067263133339
Item class	32X

**Description****Version:**

Annealed screw parts, strength class 8.8.

**Content:**

Clamping heights at 2 clamping points in mm: 178

Clamping heights at 4 clamping points in mm: 150

Step clamp: 2 pcs. size 18×125 mm; 2 pcs. size 18×160 mm

Clamping blocks, serrated L×W×H in mm: 4 pcs. size 2 (38×31×66); 4 pcs. size 3 (67×31×117)

Screws for T-slots strength class 8.8: 4 pcs. M16×18×100 mm; 4 pcs. M16×18×160 mm

Clamping spindle strength class 8.8 in mm: 4 pcs. M16×125

Hexagonal nut (1.5 d tall): 4 × M16

Washer for clamping tools: 4 × M16

Extension nut: 4 × M16

Weight in kg: 12.2

External dimensions of box in mm: 236×208×95

**Technical description**

Type of product	Clamping screw
-----------------	----------------

