


KOMET® replaceable bridge for M03Speed, Ø Dmin: 38mm

Order data

Order number	238372 38
GTIN	4047109079786
Item class	24I

Technical description

Coarse adjustment travel S	6.5 mm
Cutter circle Ø D2 forwards machining	Ø 3.2 mm
maximum speed	31000 min ⁻¹
Minimum Ø D _{min}	38
Height H	17.5 mm
Blade carrier	238374 38-50
Boring range Ø	38 - 51 mm
Micro-adjustable drilling head	238370 38
Type of product	Boring tool

Accessories

KOMET® cartridge 90° for M03SpeedForwards suitable for
M03 Size 38-50

238374 38-50

KOMET® M03Speed micro-adjustable drilling head Ø Dmin
38 mm

238370 38