


KOMET® replaceable bridge for M03Speed, Ø Dmin: 50mm

Order data

Order number	238372 50
GTIN	4047109079793
Item class	24I

Technical description

Height H	17.5 mm
Minimum Ø D _{min}	50
Blade carrier	238374 38-50
Coarse adjustment travel S	6.5 mm
Boring range Ø	50 - 63 mm
Cutter circle Ø D2 forwards machining	Ø 3.5 mm
maximum speed	24000 min ⁻¹
Micro-adjustable drilling head	238370 38
Type of product	Boring tool

Accessories

KOMET® M03Speed micro-adjustable drilling head Ø Dmin
38 mm

238370 38

KOMET® cartridge 90° for M03SpeedForwards suitable for
M03 Size 38-50

238374 38-50