

 KOMET**KOMET® arbor, SK 50, ABS® Ø d: 100mm****Order data**

Order number	239002 100
GTIN	4047109045224
Item class	29W

Description**Version:**

- Form AD/B
- Arbor balanced to Q 6.3 at 8000 rpm.
- With through coolant feed.

Standard:**DIN 69871****Supplied with:****Complete with sealing washer and conversion set for form AD.****Note:**

Further arbors with ABS® connection on request.

Technical description

Overhang A	115 mm
Projection length L ₁	95 mm
ABS® shank Ø D _s	100 mm
Adapter	SK 50
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting