

 **KOMET**
KOMET® replaceable bridge for M03Speed, Ø Dmin: 62mm

Order data

Order number	238372 62
GTIN	4047109077164
Item class	24I

Technical description

Minimum $\varnothing D_{\min}$	62
Boring range \varnothing	62 - 83 mm
Cutter circle $\varnothing D_2$ forwards machining	55 mm
Height H	23 mm
maximum speed	18500 min ⁻¹
Coarse adjustment travel S	10 mm
Blade carrier	238374 62-82
Micro-adjustable drilling head	238370 62
Type of product	Boring tool

Accessories

KOMET® cartridge 90° for M03SpeedForwards suitable for M03 Size 62-82

238374 62-82

KOMET® M03Speed micro-adjustable drilling head Ø Dmin 62 mm

238370 62