


KOMET® replaceable bridge for M03Speed, Ø Dmin: 82mm

Order data

Order number	238372 82
GTIN	4047109077157
Item class	24I

Technical description

Blade carrier	238374 62-82
Coarse adjustment travel S	10.5 mm
Cutter circle Ø D2 forwards machining	71 mm
Boring range Ø	82 - 103 mm
Height H	23 mm
maximum speed	15000 min ⁻¹
Minimum Ø D _{min}	82
Micro-adjustable drilling head	238370 62
Type of product	Boring tool

Accessories

KOMET® M03Speed micro-adjustable drilling head Ø Dmin
62 mm

238370 62

KOMET® cartridge 90° for M03SpeedForwards suitable for
M03 Size 62-82

238374 62-82