

 KOMET**KOMET® arbor, SK 40, ABS® Ø d: 25mm****Order data**

Order number	239000 25
GTIN	4047109045071
Item class	29W

**Description****Version:**

- Form AD/B
- Arbor balanced to Q 6.3 at 8000 rpm.
- With through coolant feed.

**Standard:****DIN 69871****Supplied with:****Complete with sealing washer and conversion set for form AD.****Note:**

Further arbors with ABS® connection on request.

**Technical description**

Projection length L <sub>1</sub>	19 mm
Overhang A	50 mm
ABS® shank Ø D <sub>s</sub>	25 mm
Adapter	SK 40
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting