


KOMET® arbor, HSK-A 100, ABS® Ø d: 80mm

Order data

Order number	239022 80
GTIN	4047109003576
Item class	29W

Description
Version:

- Arbor balanced to Q 6.3 at 10,000 rpm.
- With through coolant feed.

Standard:
DIN 69893
Note:

Further arbors with ABS® connection on request.

Technical description

ABS® shank Ø D _s	80 mm
Overhang A	90 mm
Projection length L ₁	61 mm
Adapter	HSK-A 100
Shank	ABS
Arbor standard	DIN 69893
Through-coolant	yes
External Ø d ₁	100 mm
Type of product	ABS mounting

