


**KOMET KUB Quatron® indexable drill ABS® shank, 3xD, Ø DC m7: 17mm**

**Order data**

Order number	235505 17
GTIN	4047109025974
Item class	24P

**Description**
**Version:**

**With ABS® shank.**

**Application:**

With indexable inserts No. 236520 – 236576.

**Supplied with:**

Clamp screws (without indexable inserts).

**Note:**

For use only under **stable** machining conditions.

**Offset-axis drilling is possible up to  $V_{max} = 0.25$  mm**, e.g. with eccentric adjusting unit No. 239010 – 239012.

Maximum  $\varnothing = D+0.5$  mm achievable by offsetting.

Further sizes available on request.

**Technical description**

ABS® shank Ø D <sub>s</sub>	50 mm
Number of cutting edges Z	1
ISO code indexable insert	SOEX 050204 13-..
Pack of insert screws	239652 6IP1 (0.6 Nm)
Reach L <sub>1</sub>	51 mm
Series	KUB Quatron®
Nominal Ø D	17

Overall length L	117 mm
Overhang L <sub>A</sub>	86 mm
Drill depth for indexable insert drill up to	3×D
Shank	ABS
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	Cross-drilling
Use for drilling	Centre drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Use for drilling	oblique spot drilling
Through-coolant	yes
Type of product	Indexable drill

## Accessories

Torx Plus® insert screw set 10 pieces Drive 6IP1	239652 6IP1
Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6