

 KOMET

KOMET® replaceable bridge for M03Speed, Ø Dmin: 100mm

Order data

Order number	238372 100
GTIN	4047109073784
Item class	24I

Technical description

Blade carrier	238374 100-166
Minimum $\varnothing D_{\min}$	100
Cutter circle $\varnothing D_2$ forwards machining	85 mm
Height H	26 mm
maximum speed	11500 min ⁻¹
Coarse adjustment travel S	15 mm
Boring range \varnothing	100 - 130 mm
Micro-adjustable drilling head	238370 100
Type of product	Boring tool

Accessories

KOMET® cartridge 90° for M03SpeedForwards suitable for
M03 Size 100-166

238374 100-166

KOMET® M03Speed micro-adjustable drilling head Ø Dmin
100 mm

238370 100