


KOMET® replaceable bridge for M03Speed, Ø Dmin: 128mm

Order data

Order number	238372 128
GTIN	4047109073791
Item class	24I

Technical description

Blade carrier	238374 100-166
Height H	26 mm
Cutter circle Ø D2 forwards machining	109 mm
maximum speed	10000 min ⁻¹
Coarse adjustment travel S	20 mm
Minimum Ø D _{min}	128
Boring range Ø	128 - 169 mm
Micro-adjustable drilling head	238370 100
Type of product	Boring tool

Accessories

KOMET® M03Speed micro-adjustable drilling head Ø Dmin
100 mm

238370 100

KOMET® cartridge 90° for M03SpeedForwards suitable for
M03 Size 100-166

238374 100-166