


**KOMET® replaceable bridge for M03Speed, Ø Dmin: 166mm**

**Order data**

Order number	238372 166
GTIN	4047109073807
Item class	24I

**Technical description**

maximum speed	8000 min <sup>-1</sup>
Minimum Ø D <sub>min</sub>	166
Height H	26 mm
Blade carrier	238374 100-166
Cutter circle Ø D2 forwards machining	166 mm
Coarse adjustment travel S	20.5 mm
Boring range Ø	166 - 206 mm
Micro-adjustable drilling head	238370 100
Type of product	Boring tool

**Accessories**

KOMET® cartridge 90° for M03SpeedForwards suitable for  
M03 Size 100-166

238374 100-166

KOMET® M03Speed micro-adjustable drilling head Ø Dmin  
100 mm

238370 100