

 KOMET

KOMET® arbor, SK 40, ABS® Ø d: 63mm

Order data

Order number	239000 63
GTIN	4047109045118
Item class	29W

Description
Version:

- Form AD/B
- Arbor balanced to Q 6.3 at 8000 rpm.
- With through coolant feed.

Standard:
DIN 69871
Supplied with:
Complete with sealing washer and conversion set for form AD.
Note:

Further arbors with ABS® connection on request.

Technical description

Overhang A	90 mm
ABS® shank Ø D _s	63 mm
Projection length L ₁	70 mm
Adapter	SK 40
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting