

 KOMET**KOMET® arbor, SK 50, ABS® Ø d: 63mm****Order data**

Order number	239002 63
GTIN	4047109045200
Item class	29W

Description**Version:**

- Form AD/B
- Arbor balanced to Q 6.3 at 8000 rpm.
- With through coolant feed.

Standard:**DIN 69871****Supplied with:****Complete with sealing washer and conversion set for form AD.****Note:**

Further arbors with ABS® connection on request.

Technical description

Projection length L ₁	29 mm
Overhang A	60 mm
ABS® shank Ø D _s	63 mm
Adapter	SK 50
Shank	ABS
Arbor standard	DIN 69871
Shape	ADB

Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Through-coolant	yes
Type of product	ABS mounting