

**Garant**
**Clamp toolholder, left-hand, Shank / insert size: 20/12mm**

**Order data**

Order number	250017 20/12
GTIN	4045197649898
Item class	21T

**Technical description**

Insert size	12 mm
Clamp, screw, spring	259035 2
Shim screw	259025 10
ISO code toolholder	DCLNR/L 2020K12
Shank size	20 mm
suitable indexable insert	CN.. 1204..
Functional width L <sub>4</sub>	25 mm
Head length L <sub>1</sub>	30 mm
Shim	259031 2
Overall length L	125 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Clamp unit Type 2	259035 2
Shim Type 2	259031 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Shim screw Type 10	259025 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500