



## Ultrasonic cleaning unit Elmasonic Easy, Type: 6

### Order data

Order number	082003 6
GTIN	4250004100688
Item class	04S

### Description

#### Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

The ultrasonic cleaning devices from the Elmasonic Easy series are powerful and ideal for beginners.

- **2 ultrasonic modes.**
- **Temperature can be adjusted in steps of 5°C.**
- **Electronic selector switch and LED display of all operating statuses.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel.**

#### Function:

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

#### Supplied with:

Without component basket.

#### Note:

Further sizes and types on request. You can find the suitable component basket under No. 082102 1 (Elmasonic Easy 1L); ultrasonic cleaning agents and anti-corrosion agents are available under 088015 – 088019.

### Technical description

Power supply	Mains-powered
IP Index of Protection	IP 20
Manufacturer's designation	Elmasonic Easy 6L

Cleaning bath height	145 mm
Nominal voltage	230 V
Item length	370 mm
Cleaning bath width	130 mm
Heating power	400 W
Item height	280 mm
Cleaning bath length	280 mm
Power consumption	150 W
Item width	225 mm
Volume	5.9 l
Type of product	Ultrasonic cleaning unit