



## Ultrasonic cleaning unit Elmasonic Easy, Type: 30

### Order data

Order number	082003 30
GTIN	4250004100725
Item class	04S

### Description

#### Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

The ultrasonic cleaning devices from the Elmasonic Easy series are powerful and ideal for beginners.

- **2 ultrasonic modes.**
- **Temperature can be adjusted in steps of 5°C.**
- **Electronic selector switch and LED display of all operating statuses.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel.**

#### Function:

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

#### Supplied with:

Without component basket.

#### Note:

Further sizes and types on request. You can find the suitable component basket under No. 082102 1 (Elmasonic Easy 1L); ultrasonic cleaning agents and anti-corrosion agents are available under 088015 – 088019.

### Technical description

Cleaning bath length	475 mm
Power supply	Mains-powered
Item width	375 mm

Volume	27.5 l
Heating power	1200 W
IP Index of Protection	IP 20
Item length	575 mm
Cleaning bath height	195 mm
Cleaning bath width	270 mm
Power consumption	300 W
Item height	330 mm
Manufacturer's designation	Elmasonic Easy 30L
Type of product	Ultrasonic cleaning unit