



Ultrasonic cleaning unit Elmasonic Easy, Type: 12

Order data

Order number	082003 12
GTIN	4250004100701
Item class	04S

Description

Version:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

The ultrasonic cleaning devices from the Elmasonic Easy series are powerful and ideal for beginners.

- **2 ultrasonic modes.**
- **Temperature can be adjusted in steps of 5°C.**
- **Electronic selector switch and LED display of all operating statuses.**
- **Acoustic and visual feedback about the operating status.**
- **Tray made of drawn stainless steel.**

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Supplied with:

Without component basket.

Note:

Further sizes and types on request. You can find the suitable component basket under No. 082102 1 (Elmasonic Easy 1L); ultrasonic cleaning agents and anti-corrosion agents are available under 088015 – 088019.

Technical description

Cleaning bath height	195 mm
Item width	315 mm
Item length	380 mm

Power consumption	200 W
Cleaning bath width	215 mm
Nominal voltage	230 V
Volume	12.9 l
Cleaning bath length	275 mm
Manufacturer's designation	Elmasonic Easy 12L
Heating power	800 W
IP Index of Protection	IP 20
Item height	280 mm
Power supply	Mains-powered
Type of product	Ultrasonic cleaning unit