



Drying unit, Type: 12



Order data

Order number	082005 12
GTIN	4250004103788
Item class	04S

Description

Version:

Elma Dry drying units are designed for use in production facilities, workshops and service areas. After cleaning in the ultrasonic bath, the items in the Elma component basket are first rinsed in the Elma Sink (No. 082004) and then dried easily and conveniently in the Elma Dry. Its **cold/hot-air blower (70°C)** ensures that even delicate parts can be dried gently. In cold-air mode, the parts can also be cooled down quickly. The cover includes ventilation slits that maximise the air turbulence and discharge the humid air to the outside. At the same time, the cover reduces energy consumption. The **dust filter** on the underside of the base is replaceable and prevents recontamination of the cleaned parts due to dust in the room air (filter fineness 33ppi). Due to the safety shutdown when the limit temperature is reached, Elma Dry units are both **extremely safe and gentle on their contents**.

Suitable for:

Component basket No. 082101: Size 12

Supplied with:

Without component basket. 1 pc. Elma Dry 120; 1 pc. cover; 1 pc. mains cable with IEC power connection (2 m long); 1 pc. operating instructions.

Note:

Suitable component baskets can be found under No. 082101.

Technical description

Power consumption	570 W
Power supply	Mains-powered
Cleaning bath width	215 mm
Heating power	550 W
Length of component basket	275 mm
Cleaning bath height	195 mm
Item height	322 mm
On/Off switch	yes
Cleaning bath length	275 mm
Nominal voltage	220 - 240 V
Manufacturer's designation	Elma Dry 120
Item length	362 mm
Weight	6.1 kg
Item width	285 mm
Volume	12 l
Air flow volume	160 m ³ /h
Warm-up time	~ 15 min
maximum temperature	70 °C
maximum load	7 kg
Type of product	Cleaning device