


KOMET KUB Quatron® indexable drill ABS® shank, 3xD, Ø DC m7: 31 mm

Order data

Order number	235505 31
GTIN	4047109026742
Item class	24P

Description
Version:

With ABS® shank.

Application:

With indexable inserts No. 236520 – 236576.

Supplied with:

Clamp screws (without indexable inserts).

Note:

For use only under **stable** machining conditions.

Offset-axis drilling is possible up to $V_{max} = 0.25$ mm, e.g. with eccentric adjusting unit No. 239010 – 239012.

Maximum $\varnothing = D+0.5$ mm achievable by offsetting.

Further sizes available on request.

Technical description

Number of cutting edges Z	1
ISO code indexable insert	SOEX 090408 32-..
Reach L_1	93 mm
ABS® shank $\varnothing D_s$	50 mm
Pack of insert screws	239652 15IP1 (2.8 Nm)
Series	KUB Quatron®
Nominal $\varnothing D$	31

for inch Ø	1 7/32 in
Overall length L	164 mm
Overhang L _A	133 mm
Drill depth for indexable insert drill up to	3×D
Shank	ABS
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	Cross-drilling
Use for drilling	Centre drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Use for drilling	oblique spot drilling
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torque screwdriver, fixed setting set torque 2,8 N·m	211750 2,8
Torx Plus® insert screw set 10 pieces Drive 15IP1	239652 15IP1