

Garant
Lever lock toolholder, right-hand, Shank / insert size: 16/12 mm

Order data

Order number	250018 16/12
GTIN	4045197649942
Item class	21T

Description

Lever lock toolholder 16/12 mm ISO code toolholder: PCLNR/L 1616H12
 suitable indexable insert: CN.. 1204..
 Functional width L₄: 20 mm
 Head length L₁: 25 mm
 Overall length L: 100 mm
 Shim: 259031 2

Technical description

Lever	259015 2
ISO code toolholder	PCLNR/L 1616H12
Insert size	12 mm
Shank size	16 mm
Shim	259031 2
Functional width L ₄	20 mm
Shim pins pack	259044 2
Lever screw	259018 8
Head length L ₁	25 mm
Shim punches pack	259047 2
suitable indexable insert	CN.. 1204..

Overall length L	100 mm
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95°
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 8	259018 8
Set of shim pins 10 pieces Type 2	259044 2
Shim Type 2	259031 2
Shim punches set 10 pieces Type 2	259047 2