

Garant
Clamp toolholder, right-hand, Shank / insert size: 32/12mm

Order data

Order number	250016 32/12
GTIN	4045197681720
Item class	21T

Technical description

ISO code toolholder	DCLNR/L 3232P12
Shim screw	259025 10
Insert size	12 mm
Clamp, screw, spring	259035 2
Shim	259031 2
Shank size	32 mm
Functional width L ₄	40 mm
Head length L ₁	34 mm
suitable indexable insert	CN.. 1204..
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamp unit Type 2	259035 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Shim Type 2	259031 2
Shim screw Type 10	259025 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500