

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 32/12mm****Order data**

Order number	250019 32/12
GTIN	4045197654342
Item class	21T

**Technical description**

Shank size	32 mm
Lever screw	259018 2
Functional width L <sub>4</sub>	40 mm
suitable indexable insert	CN.. 1204..
ISO code toolholder	PCLNR/L 3232P12
Shim pins pack	259044 2
Shim punches pack	259047 2
Lever	259015 2
Shim	259031 2
Insert size	12 mm
Head length L <sub>1</sub>	30 mm
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 2	259031 2
Set of shim pins10 pieces Type 2	259044 2
Lever Type 2	259015 2
Shim punches set10 pieces Type 2	259047 2
Lever screw Type 2	259018 2