

**Cylinder padlock individual keys, Body Ø: 40mm****Order data**

Order number	GG5881 40
GTIN	4067263140702
Item class	GGN

Description**Version:**

Abrasive roller Ø 100x100 mm with flap strips of abrasive cloth. Mounting bore Ø 19 mm with multiple splines.
similar to 568480.

Function:

Individual keys means each key can open and close only **one** lock or cylinder, i.e. the key is unique.

Supplied with:

10 pcs. padlocks with 3 keys each.

Technical description

Locking	individual keys
Shackle, double lever mechanism	yes
Material of the housing	Brass
Lock mechanism	rust-free precision lock mechanism
compatible with integrated locking systems	no
suitable for lock barrels	no
Material of the band	Chrome-plated steel

Data sheet

Number of keys	30
Hoop Ø	6 mm
with keyhole cover	no
Body Ø	40 mm
Hoop hardened	yes
Number of locks	10
Type of product	Padlock

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG5881-40>