


**KOMET KUB Quatron® indexable drill ABS® shank, 4xD, Ø DC m7: 26mm**

**Order data**

Order number	235507 26
GTIN	4047109091207
Item class	24P

**Description**
**Application:**

With indexable inserts No. 236520 – 236576.

**Note:**

For use only under **stable** machining conditions.

**Offset-axis drilling is possible up to  $V_{\max} = 0.25 \text{ mm}$** , e.g. with eccentric adjusting unit No. 239010 – 239012.

Maximum  $\varnothing = D + 0.5 \text{ mm}$  achievable by offsetting.

Further sizes available on request.

**Technical description**

Number of cutting edges Z	1
Reach $L_1$	104 mm
ABS® shank $\varnothing D_s$	50 mm
Pack of insert screws	239652 8IP1 (1.3 Nm)
ISO code indexable insert	SOEX 07T308 23-...
Series	KUB Quatron®
Nominal $\varnothing D$	26
Overall length L	170 mm
Overhang $L_A$	139 mm
Drill depth for indexable insert drill up to	4xD

Shank	ABS
Through-coolant	yes
Type of product	Indexable drill

---

## Accessories

Torx Plus® insert screw set10 pieces Drive 8IP1	239652 8IP1
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3