

**Garant**
**Lever lock toolholder, right-hand, Shank / insert size: 20/12mm**

**Order data**

Order number	250020 20/12
GTIN	4045197650054
Item class	21T

**Technical description**

Shim pins pack	259044 2
Shank size	20 mm
Lever	259015 2
Shim punches pack	259047 2
Lever screw	259018 2
Insert size	12 mm
suitable indexable insert	CN.. 1204..
ISO code toolholder	PCBNR/L 2020K12
Functional width L <sub>4</sub>	25 mm
Head length L <sub>1</sub>	28 mm
Shim	259031 2
Overall length L	125 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 2	259015 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2
Lever screw Type 2	259018 2