

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 20/12mm****Order data**

Order number	250021 20/12
GTIN	4045197650078
Item class	21T

**Technical description**

suitable indexable insert	CN.. 1204..
ISO code toolholder	PCBNR/L 2020K12
Shim punches pack	259047 2
Shim	259031 2
Shim pins pack	259044 2
Head length L <sub>1</sub>	28 mm
Insert size	12 mm
Functional width L <sub>4</sub>	25 mm
Shank size	20 mm
Lever screw	259018 2
Lever	259015 2
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

## Data sheet

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

Shim punches set 10 pieces Type 2	259047 2
Lever Type 2	259015 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Lever screw Type 2	259018 2