

Garant**Lever lock toolholder, right-hand, Shank / insert size: 20/12mm****Order data**

Order number	250022 20/12
GTIN	4045197650092
Item class	21T

Technical description

Lever	259015 2
Shim	259031 2
ISO code toolholder	PCKNR/L 2020K12
Head length L ₁	28 mm
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Shim punches pack	259047 2
Lever screw	259018 2
Shim pins pack	259044 2
Functional width L ₄	25 mm
Shank size	20 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim punches set 10 pieces Type 2	259047 2
Set of shim pins 10 pieces Type 2	259044 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Lever Type 2	259015 2