

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 20/09mm

Order data

Order number	250037 20/09
GTIN	4045197650221
Item class	21T

Technical description

Lever screw	259018 9
Centre offset L_3	13 mm
ISO code toolholder	A20Q PCLNR/L09
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	9 mm
suitable indexable insert	CN.. 09T3..
Lever	259015 11
Overall length L	180 mm
Clamping height L_2	18 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2
Lever screw Type 10	259018 10
Lever Type 11	259015 11
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500