

**Garant**
**Lever lock toolholder, left-hand, Shank / insert size: 32/16mm**

**Order data**

Order number	250019 32/16
GTIN	4045197650030
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	40 mm
Shim	259031 35
Insert size	16 mm
Head length L <sub>1</sub>	40 mm
Shank size	32 mm
Shim pins pack	259044 6
Lever	259015 12
suitable indexable insert	CN.. 1606..
ISO code toolholder	PCLNR/L 3232P16
Lever screw	259018 11
Shim punches pack	259047 4
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever screw Type 11	259018 11
Lever Type 12	259015 12
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4