

**Garant**
**Lever lock toolholder, right-hand, Shank / insert size: 25/12mm**

**Order data**

Order number	250024 25/12
GTIN	4045197650146
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	32 mm
Shim pins pack	259044 2
Lever screw	259018 2
Shank size	25 mm
ISO code toolholder	PCSNR/L 2525M12
Lever	259015 2
Shim	259031 2
Insert size	12 mm
Head length L <sub>1</sub>	33 mm
suitable indexable insert	CN.. 1204..
Shim punches pack	259047 2
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of shim pins10 pieces Type 2	259044 2
Shim Type 2	259031 2
Lever screw Type 2	259018 2
Lever Type 2	259015 2
Shim punches set10 pieces Type 2	259047 2