

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 40/16mm

Order data

Order number	250037 40/16
GTIN	4045197654410
Item class	21T

Technical description

ISO code toolholder	A40T PCLNR/L16
Shim punches pack	259047 4
Shim	259031 35
Centre offset L_3	27 mm
Insert size	16 mm
Lever	259015 12
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Lever screw	259018 11
suitable indexable insert	CN.. 1606..
Shim pins pack	259044 6
Overall length L	300 mm
Clamping height L_2	38.5 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 35	259031 35
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Lever Type 12	259015 12
Lever screw Type 11	259018 11
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500