

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 50/16mm


Order data

Order number	250037 50/16
GTIN	4045197654427
Item class	21T

Technical description

Shim pins pack	259044 6
Lever	259015 12
Insert size	16 mm
Lever screw	259018 11
Shim	259031 35
Shim punches pack	259047 4
ISO code toolholder	A50U PCLNR/L16
Centre offset L_3	35 mm
Minimum pre-drill $\varnothing D_{min}$	63 mm
suitable indexable insert	CN.. 1606..
Overall length L	350 mm
Clamping height L_2	48 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	50 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500