

Round sling, orange, 10,000 kg, Usable length: 1,5m**Order data**

Order number	086285 1,5
GTIN	2050001735911
Item class	08Z

Description**Version:**

Extremely wear-resistant round lifting slings (EN 1492-2) with seamless, single-layer sleeving.

Application:

For lifting and transporting components.

Note:

Available up to the following lift ratings: 150 t (polyester), 180 t (Dyneema).

Technical description

Circumference	3 m
Usable length	1.5 m
Sling width	91 mm
Safe working load simple direct lift WLL	10000 kg
Safe working load simple looped lift WLL	8000 kg
Safe working load double WLL up to 7°	20000 kg
Safe working load double WLL 7° – 45°	14000 kg
Safe working load double WLL 45° – 60°	10000 kg
Type of product	Round slings