



LED inspection lamp with battery, Lamp head Ø: 25mm



Order data

Order number	081421 25
GTIN	2050001694911
Item class	08C

Description

Version:

Exceptionally robust inspection lamps made from **solid aluminium** with LED lamp head. Battery grip including flexible neck, splash-proof. 1 pc. stainless steel inspection mirror 40x65 mm unbreakable.

Technical description

Battery type	LR6
Illumination	180 lm
Article no of the battery / rechargeable battery fitted	081559 LR6
ATEX zone	no
Overall length	600 mm
Number of batteries contained	2
Head Ø	25 mm
Power supply	Battery-powered

Spread angle	100 degrees
Type of product	Inspection lamp

Accessories

Button cell / special battery Battery type SL760	081560 SL760
Magnetic base	081413
Alkaline-manganese batteries International size LR6	081561 LR6
Mirror set for LED inspection lamp / workshop lamp set2 pieces	081427