

Garant
Arbor 90°, cylindrical with IC long, Type: 10

Order data

Order number	239745 10
GTIN	4045197593238
Item class	23A

Description
Version:

Version suitable for NC with straight shank \varnothing for standard arbors especially in **hydraulic chucks** or **high precision collet chucks** for very high accuracy and process reliability.

Note:

Observe the mounting size of the holder and reaming heads. For further arbors see No. 210550 – 210582 and No. 212000.

Shank: DIN 6535 HA to h6

suitable for through hole \varnothing : 10 - 12.7 mm

suitable for blind hole \varnothing : 14 - 16.2 mm

Overall length L: 120 mm

Reach L_1 : 65 mm

Shank $\varnothing D_s$ h6: 16 mm

recommended tightening torque: 5 N·m

Technical description

Reach L_1	65 mm
suitable for through hole \varnothing	10 - 12.7 mm
suitable for blind hole \varnothing	14 - 16.2 mm
Shank $\varnothing D_s$ h6	16 mm
recommended tightening torque	5 N·m
Overall length L	120 mm
Series	TopCut

Through-coolant	yes
Shank	DIN 6535 HA to h6
Type of product	Threaded copy mill arbor