



LED headlamp, Type: H7.2



Order data

Order number	081486 H7.2
GTIN	4029113729703
Item class	04B

Description

Version:

Powerful high-quality LED headlamps **Power illumination**, can be steplessly focussed and dimmed. With several illumination modes.

IP Index of Protection: IP X6

Manufacturer's designation: H7.2

ATEX zone: no

Illumination: 20 - 250 lm

Working life: 5 - 30 h

Number of batteries contained: 4

Battery type: Micro, AAA

Technical description

Weight	165 g
Manufacturer's designation	H7.2
Smart Light Technology (SLT)	yes
Illumination	20 - 250 lm
Power supply	Battery-powered
Advanced Focus System (AFS)	yes
Working life	5 - 30 h

Illumination range	50 - 160 m
Battery type	Micro, AAA
Including belt pocket	no
Number of batteries contained	4
Head Ø	35 mm
Rapid Focus	yes
IP Index of Protection	IP X6
ATEX zone	no
chemical composition	Alkaline manganese
rechargeable	no
Dimmable lighting	yes
Type of product	Headlamp