



## KUB Pentron® indexable drill Plain shank, 4×D, Ø DC m7: 34,5mm



### Order data

Order number	236601 34,5
GTIN	4047109201408
Item class	24P

### Description

#### Version:

- **Very high performance and long tool life thanks to optimised base body strength and special surface treatment.**
- **Best dimensional accuracy under very difficult drilling conditions.**
- **Stock costs reduced because internal and external inserts are identical.**
- **Offset-axis drilling is possible up to  $V_{max} = 0.25$  mm. Maximum  $\varnothing = D + 0.5$  mm achievable by offsetting.**

**Bore tolerance:**  $\varnothing D - 0.1 / + 0.3$

#### Application:

- **Under extreme machining conditions.**

With indexable inserts No. 236605 – 236610.

#### Supplied with:

Clamp screws (without indexable inserts).

#### Note:

Version 2×D and 3×D with ABS® also available on request in imperial sizes.

Version with PSC shank available on request.

### Technical description

Number of cutting edges Z	1
Shank $\varnothing D_s$	40 mm
Reach $L_1$	140 mm
ISO code indexable insert	SOGX 110408 38-...
Pack of insert screws	239652 15IP1 (2.8 Nm)

Shank length $L_s$	68 mm
Series	KUB Pentron®
Nominal $\varnothing D$	34.5
Overhang $L_A$	166 mm
Drill depth for indexable insert drill up to	4×D
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

## Accessories

Torque screwdriver, fixed setting set torque 2,8 N·m	211750 2,8
Torx Plus® insert screw set 10 pieces Drive 15IP1	239652 15IP1
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP