

**Flat magnet 2-part set with threaded stud, Neodymium, Ø: 43mm****Order data**

Order number	085937 43
GTIN	4069515000017
Item class	08Q

Description**Version:**

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

Application:

On painted surfaces, will not scratch or slip.

Technical description

Height	6 mm
Ø	43 mm
Material of the surface	rubberised
Thread	M6
Height with thread	21 mm
Nominal clamping force	85 N
Material of the magnet core	Neodymium

Type of product

Flat gripper magnet