

**Flat magnet 2-part set with threaded socket flat, Neodymium, Ø: 88mm****Order data**

Order number	085939 88
GTIN	4069515000109
Item class	08Q

Description**Version:**

- **Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.**
- **Corrosion resistance and surface protection due to the rubberised surface.**
- **Rubberisation increases the lateral holding forces.**
- **Neodymium magnetic core.**

Application:

On painted surfaces, will not scratch or slip.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Height with thread	8.5 mm
Nominal clamping force	420 N
Height	8.5 mm
Thread	M8
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

